



## Detectores de película plana de 500 ohmios



**Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.**

**All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.**



Labfacility son actualmente detectores de película plana multi-sourcing con el fin de garantizar que podemos mantener un servicio de suministro a nuestros clientes sin afectar la calidad o funcionalidad en el futuro previsible.

Todos los detectores de película plana suministrados, aunque difieren en apariencia y embalaje en algunos casos, cumplirán con las especificaciones publicadas en nuestras hojas de datos.

## Specifications

<b>Element/hot junction</b>	Thin film construction
<b>Element</b>	Pt500 to IEC751
<b>Max. Temperature</b>	+500°C
<b>Min. Temperature</b>	-50°C
<b>Tolerance</b>	Class B or A available in accordance with IEC 60751
<b>Features #1</b>	Resists vibration & shock