



Detectores de película plana de 500 ohmios



Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.

All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.



Labfacility son actualmente detectores de película plana multi-sourcing con el fin de garantizar que podemos mantener un servicio de suministro a nuestros clientes sin afectar la calidad o funcionalidad en el futuro previsible.

Todos los detectores de película plana suministrados, aunque difieren en apariencia y embalaje en algunos casos, cumplirán con las especificaciones publicadas en nuestras hojas de datos.

Specifications

| | |
|-----------------------------|---|
| Element/hot junction | Thin film construction |
| Element | Pt500 to IEC751 |
| Max. Temperature | +500°C |
| Min. Temperature | -50°C |
| Tolerance | Class B or A available in accordance with IEC 60751 |
| Features #1 | Resists vibration & shock |