

Termmetro de horno digital DOT



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

TENGA EN CUENTA: El plazo de entrega ser de 7-10 das hbiles al elegir la calibracin

Lectura de temperatura en solo 5 segundos

Se suministra completo con sonda de penetracin

Gran pantalla LCD

Alarma de temperatura audible ruidosa de 70dB

El termmetro de horno digital DOT es un termmetro de cocina fcil de usar que muestra tanto la temperatura actual como la alarma audible. Simplemente ajuste la temperatura deseada usando los botones, inserte la sonda en su comida, el DOT emitir un pitido y la pantalla parpadear cuando se alcance la temperatura.

El DOT incorpora una gran pantalla LCD y una fuerte alarma audible de 70 dB, lo que lo hace ideal para su uso en cocinas profesionales ocupadas.

Alojado en un estuche duradero y resistente al agua, el DOT est diseado para sentarse en una encimera usando el soporte plegable o para conectarse a un aparato usando las almohadillas magnticas en la parte posterior del instrumento.

Cada unidad se suministra con una sonda de penetracin de 114 mm con un cable trenzado de acero inoxidable de 1,2 metros. Consulte a continuacin las especificaciones completas.

Rango: -50 a 300C

Resolucin: 1 C/F

Precisin: 1 C (-20 a 120 C)

Batera: 2 x 1.5 voltios AAA

Duracin de la batera: 5000 horas

Volumen de alarma: 70dB

Tipo de sensor: termistor

Pantalla: LCD personalizada

Dimensiones: 20 x 80mm

Peso: 95 gramos

Material de la caja: plstico ABS

Garanta: un ao

Resistencia al agua / polvo: proteccin IP65

Escala de medicin: Celsius / Fahrenheit

Specifications



Product Code	XE-3938-001
General Description	DOT Digital Oven Thermometer
Sensor Type	thermistor
Battery	2 x 1.5 volt AAA
Housing	ABS plastic
Display	LCD
Resolution	1 °C/°F
Max. Temperature	+120°C
Min. Temperature	-20°C
IP Rating	IP65
Accuracy	±1°C (-20 to 120 °C)
Dimensions	20 x 80mm
Weight	95 grams
Alarm volume	70dB
Features #1	Guarantee: one year
Features #2	supplied with a 114 mm penetration probe with a 1.2 metre stainless steel braided lead