


Termopares de punta soldada expuesta de fibra de vidrio de alta temperatura ANSI con terminación de enchufe estándar



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Necesita calibrar su sensor de temperatura?

Trazable a los estándares de calibración ISO17025 (UKAS), Labfacility ofrece la opción de una calibración trazable de 3 o 5 puntos utilizando nuestras instalaciones de calibración internas.

Tenga en cuenta que si agrega una opción de calibración a su pedido, se comunicará con usted con respecto a la información de entrega.

Características técnicas**Specifications**

General Description	Fast response, welded exposed junction. Good temperature resistance (not suitable in fluids).
Thermocouple Type	K
Thermocouple Junction	Exposed
Cable Length	5, 10 or 20-metre-long
Cable Type	high temperature glassfibre insulated twisted cable
Core / Strands	1/0.711mm conductors (21awg)
Cable Termination	Standard plug termination
Max. Temperature	+700°C
Min. Temperature	0°C
Tolerance	Tolerance to ANSI MC96.1 Class 2
Standards Met	Colour code to ANSI MC96.1