




PFA aislado doble torcido IEC Exposed Junction termopar con enchufe moldeado - Tipo K, T



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

El tapn moldeado proporciona una construccin robusta y proporciona una terminacin impermeable.

Necesita calibrar su sensor de temperatura?

Trazable a ISO17025 estndares de calibracin (UKAS), Labfacility ofrece una opcin de calibracin trazable de 3 o 5 puntos utilizando nuestra instalacin de calibracin interna, puede seleccionar cualquier punto de temperatura entre -10 C y + 200 C.

Tenga en cuenta que si agrega una opcin de calibracin a su pedido, se le contactar con respecto a la informacin de entrega.

Specifications

General Description	Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
Sensor Type	Exposed Junction
Thermocouple Type	K or T
Cable Length	1, 2, 3m
Cable Type	PFA insulated conductors twisted together
Core / Strands	1/0.2 mm, 1/0.3mm, 1/0.5mm
Termination Type	Miniature moulded flat pin plug, colour coded 'green' in accordance IEC specification
Max. Temperature	+260°C
Min. Temperature	-75°C
Tolerance	Class 1
Standards Met	Colour code (cores & jacket) to IEC-584-3
Connector Type	Plug
Connector Size	Miniature (moulded-on)