

## GM816 Anemmetro Anemmetro Anemmetro / Anemmetro Digital



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**GM816 Anemmetro Anemmetro Anemmetro / Anemmetro Digital**

Ideal para fines industriales y domsticos, como medir la velocidad del viento y la temperatura de la CPU, ventiladores de computadora, aires acondicionados, sopladores de aire, etc.

## Specifications

|                                 |   |
|---------------------------------|---|
| <b>Product Code</b>             | XE-4003-001   |
| <b>Model</b>                    | GM816 Anemometer Wind Meter Anemometer / Digital Anemometer     |
| <b>Accuracy</b>                 | +/- 5%  |
| <b>Air Temp: Accuracy</b>       | +/- 2°C, +/- 3.6F   |
| <b>Air Temp: Range</b>          | -10~45°C, 14~113°F  |
| <b>Air Temp: Resolution</b>     | Resolution 0.2°C, 0.36°F  |
| <b>Air Velocity: Range</b>      | 0.3 - 30m/s, 0 - 90km/h, 0 - 5860ft/min, 0 - 65mph, 0 - 55Knots |
| <b>Air Velocity: Resolution</b> | 0.1m/s, 0.3km/h, 19ft/min, 0.2mph, 0.2Knots                     |
| <b>Air Velocity: Threshold</b>  | 0.1m/s, 0.3km/h, 39ft/min, 0.2mph, 0.1Knots                     |
| <b>Battery</b>                  | 1 x 3V CR2032 battery (Not Included)                            |
| <b>Colour</b>                   | Yellow / Black  |
| <b>Current Consumption</b>      | 3mA Approx  |
| <b>Dimensions</b>               | 10.5 x 4.5 x 2 cm / (4.13 x 1.77 x 0.79)                        |
| <b>Operating Humidity</b>       | less than or equal to 90%RH                                     |
| <b>Operating Temperature</b>    | -10~45°C (14~113°F)   |
| <b>Weight</b>                   | 105g / 3.7oz  |
| <b>Storage Temperature</b>      | -40~60°C, -40~140°F   |
| <b>Thermometer</b>              | NTC Thermometer   |