


## Medidores de temperatura del termómetro bimetálico - Estilo de entrada trasera con bolsillo BSP de 1/2 "



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**\*\*Químicos–Calderas–Hornos–Congeladores–Camiones cisterna-Alimentos-Bebidas-Lácteos-Elaboración de cerveza-Ambientes de temperatura controlada\*\***

**Para tamanos de diámetro de vástago que no sean de 8 mm, utilice nuestro formulario de construcción personalizado utilizando el botón azul de arriba para solicitar una cotización.**

Resistente clase industrial 1, caja de acero inoxidable y bisel de bayoneta con 316 tallos de acero inoxidable. Fabricado en tamanos de cara de 100 mm con varias longitudes y diámetros disponibles. La temperatura oscila entre -20 °C y 200 °C.

1 año de garantía ofrecida para piezas de trabajo / por defecto - Micro Adjustable Pointer

Certificado de calibración opcional

Hecho a medida a pedido en aproximadamente 4 semanas. Después de realizar su pedido, se le contactará con un plazo de entrega.

### Características técnicas

## Specifications

<b>Accuracy</b>	Class 1 (1% F.S..D.)
<b>Dial Size</b>	100mm
<b>Construction</b>	Flush fitting bayonet locking case and bezel
<b>Measuring Element</b>	Bi-Metalic coil
<b>Ranges °C</b>	-20 to +40°C, 0 to +100°C, 0 to +120°C, 0 to +200°C
<b>Over Limit Range</b>	130% full scale
<b>Stem / Bulb</b>	316 Stainless steel
<b>Case / Bezel ring</b>	Stainless steel AISI 316L
<b>Window</b>	Glass
<b>Dial</b>	Aluminium, black figures on white
<b>Pointer</b>	Aluminium, black

<b>Movement</b>	Direct drive on back entry
<b>Ambient Temperature</b>	-10°C....+50°C
<b>Temperature Effect</b>	max...0,3% / 10°C
<b>Protection EN 60 529</b>	IP65