



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Conector de termopar Panel de aluminio con enchufes en miniatura ANSI tipo J



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Paneles de conectores de termopar en miniatura preensamblados

Una gama de conjuntos de paneles horizontales en miniatura preensamblados diseñados para su uso con termopares o cables con enchufes en miniatura. Son robustos y perfectos para el montaje en salas de control, bancos de pruebas, aplicaciones de laboratorio, salas de control y ms. Admiten cdigos de calibracin que incluyen K, J, T y N con enchufes de cable rpido y pueden acomodar circuitos de 1 a 24 vas, con un rango de temperatura mximo de hasta +120 C.

Se suministra preinstalado con

[enchufes de fascia en miniatura](#)

Circuitos de 1 a 24 vas

Calibracin tipo K, J, T y N disponible

Temperatura mxima 120C

Aplicaciones tpicas

Fabricantes de equipos originales

Constructores de paneles de instrumentacin

Salas de control

Bancos de pruebas y patines

Tabla de tallas

1 VA: 45 mm de alto x 40 mm de ancho
2 VAS: 45 mm de alto x 55 mm de ancho
3 VAS: 45 mm de alto x 70 mm de ancho
4 VAS: 45 mm de alto x 85 mm de ancho

5 VAS: 45 mm de alto x 100 mm de ancho
6 VAS: 45 mm de alto x 115 mm de ancho
8 VAS: 45 mm de alto x 145 mm de ancho
10 VAS: 45 mm de alto x 175 mm de ancho

12 VAS: 45 mm de alto x 205 mm de ancho
16 VAS: 75 mm de alto x 145 mm de ancho
18 VAS: 75 mm de alto x 160 mm de ancho
20 VAS: 75 mm de alto x 175 mm de ancho

24 VAS - 75 mm de alto x 205 mm de ancho

Caractersticas tcnicas

Specifications



General Description	A selection of miniature IEC pre-assembled thermocouple panels, 1-24 way, to suit your specific application. All fascia mounting sockets are polarised by means of unequally sized pins
Thermocouple Type	J ANSI
Connector Size	Miniature
Connector Type	Fascia Mounting Socket
Colour	Black
Max. Temperature	120°C
+Positive Contact	Iron
-Negative Contact	Copper Nickel
Standards Met	BS EN 50212:1997. RoHS