

## Sensor de termistor de parche autoadhesivo



[Click here to view product](#)

<b>Product Code</b>	XE-9855
<b>General Description</b>	Suitable for general purpose industrial & commercial use
<b>Sensor Type</b>	Silicone rubber patch with self-adhesive foil backing
<b>Thermistor</b>	10K NTC Thermistor
<b>BETA 25/85</b>	3977K
<b>Patch dimensions</b>	L40 x W15mm
<b>Cable Length</b>	1, 2 or 5m
<b>Cable Type</b>	PTFE insulated twisted leads
<b>Core / Strands</b>	7/0.2mm
<b>Cable Termination</b>	Bare Tails

<b>Max. Temperature</b>	+150Å°C
<b>Min. Temperature</b>	-50Å°C
<b>Accuracy</b>	+/- 0.2K (over 0-70Å°C)
<b>Number of Wires</b>	2