

## Sensor de termistor de alambre hermeticamente sellado



[Click here to view product](#)

<b>Product Code</b>	XE-9874
<b>General Description</b>	An IP67 sensor that is hermetically sealed for use in corrosive or wet environments
<b>Sensor Type</b>	Hermetically sealed thermistor
<b>Thermistor</b>	10K NTC Thermistor
<b>BETA 25/85</b>	3977K
<b>Cable Length</b>	1, 2 & 5m
<b>Cable Type</b>	2 wire flexible 7/0.2mm stranded conductors (24AWG) with 75mm tails
<b>Core / Strands</b>	7/0.2mm (24AWG)
<b>Cable Termination</b>	75mm Bare Tails
<b>Max. Temperature</b>	+150Å°C

<b>Min. Temperature</b>	-30Â°C
<b>IP Rating</b>	67
<b>Accuracy</b>	+/- 0.2K (over 0-70Â°C)
<b>Important Information</b>	Pressure tested at 40 PSI as standard