


## Sensor RTD de montaje en superficie



[Click here to view product](#)

|                            |  |
|----------------------------|--|
| <b>Product Code</b>        | XE-7700                                    |
| <b>General Description</b> | Stripped 75mm tails as standard            |
| <b>Sensor Type</b>         | Pt100                                      |
| <b>Fitting</b>             | 3mm mounting hole                          |
| <b>Cable Type</b>          | PFA  |
| <b>Termination Type</b>    | Bare Tails or Miniature 3-Pin Plug Options |
| <b>Max. Temperature</b>    | 230Â°C                                     |
| <b>Min. Temperature</b>    | -50Â°C                                     |
| <b>Tolerance</b>           | Class A                                    |
| <b>Length</b>              | 1M, 2M or 5M Lead                          |

|                        |                                 |
|------------------------|---------------------------------|
| <b>Number of Wires</b> | 4 wire or 3 wire with connector |
|------------------------|---------------------------------|